





1	Top cover, PAR
2	Housing PPS
3	Element, copper alloy with tin plated integrated heat sink



Section A - A



iMaXX ref.	Rating [A]	Volt [V]	Color
L020J	20	32	light blue
L025J	25	32	white
L030J	30	32	pink
L040J	40	32	green
L050J	50	32	red
L060J	60	32	yellow


Revisions

Date	Type	Drawn	Date	Appr.
a 02/03	add 25A	Checked	11/99	GRH
b 08/07	re-drawn	Standards	05/17	BE
c 05/17	added rated voltage	Approved	05/17	AdH



Scale 2 : 1

Projection



Tolerance
± 0.2 mm unless
otherwise noted

Title

Drawing type

Drawing number

Sheet

Layers / Sheet

L - J series, japOTO SlowBlow fuse

schematic

L - J drawing 1

1 of 1

0 1 2 4 6 7 8 9

Sheet 01