



序号/RevNo.	名称/Title	文件编号/File No.
1	XY104塑件	QJ/XYT-2138101
2	XY104螺丝 (与XY306螺丝共用)	QJ/XYT-2127101
3	XY104端子	QJ/XYT-2138103
4	XY104铜方块	QJ/XYT-2138104



Technical data:

Wire range: 22-12AWG 2.5mm²

Voltage&Current: 300V 15A

Withstand Voltage: AC2000V/Min

Contact resistance: ≤20mΩ

Poles: (2P, 3P-24P)

Pitch: 5.0mm(.197")



Materials

Housing: PA66 (UL 94V-0)

Solder Pin: Brass, Tin Plated

Wire Cage: Brass, Nickel Plated

Screw: M2.5, Steel (A3), Zinc Plated



PCB LAY OUT

设计/Designed by		绘图/Drawing by		审核/Checked by		批准/Approved by		未注公差 General Tolerance	
图名/Title		文件编号/File No.		QJ/XYT-2238100		页序/Sheet		X, ±0.2 .X, ±0.1 .XX, ±0.05 .XXX, ±0.01	X, ° ±0° .X, ° ±1° .XX, ° ±0.5° .XXX, ° ±0.5°
XY104 产品图		QJ/XYT-2238100		页序/Sheet				单位/units: mm	
备注/Remark									

设计/Designed by: 绘图/Drawing by: 审核/Checked by: 批准/Approved by: 未注公差/General Tolerance: X, ±0.2 .X, ±0.1 .XX, ±0.05 .XXX, ±0.01 X, ° ±0° .X, ° ±1° .XX, ° ±0.5° .XXX, ° ±0.5° 单位/units: mm

XY104 产品图 QJ/XYT-2238100 页序/Sheet

备注/Remark