




序号/RevNo.	名称 /Title	文件编号/File No.
1	XY126螺丝	
2	XY126簧片	
3	XY126V端子	
4	XY126V塑件5.0	



300V 10A 26-14AWG 2.5mm²
Poles: 2P&3P-24P
Pitch: 5.0mm(.197")

Materials
Housing: PA66(UL 94V-0)
Wire Protector: Stainless Steel
Solder Pin: Brass,Tin Plated
Screw: M2.5,Steel,Zinc Plated
Torque: 0.4N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD				x.	±0.2	x."	±2°
				.x	±0.1	.x°	±1°
				.xx	±0.05	.xx°	±0.5°
				.xxx	±0.01		
图名/Title		文件编号/File No.					
XY126V-5.0		QJ/XYT-2221100					
产品图		页序/Sheet					
备注 /Remark				单位/Units: mm			

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------