




序号/RevNo.	名称/Title	文件编号/File No.
1	XY304螺丝	QJ/XYT-2150101
2	XY127铜方块 (与XY304铜方块共用)	QJ/XYT-2150102
3	XY127R 端子	QJ/XYT-2139201
4	XY127 塑件	QJ/XYT-2139102



300V 12A 16-14AWG 1.5mm²
Poles: 2P&3P-24P
Pitch: 5.0mm(.197")

Materials
Housing: PA66(UL 94V-0)
Wire Cage: Brass,Nickel plated
Solder Pin: Brass,Tin Plated
Screw: M3,Steel,Zinc Plated
Torque: 0.5N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
				x. ±0.2	x.° ±2°
 新莱亚电子 XINLAIYA ELECTRONIC CO., LTD	XY127R 产品图	图名/Title	文件编号/File No. QJ/XYT-2239200	.x ±0.1	.x° ±1°
				.xx ±0.05	.xx° ±0.5°
				.xxx ±0.01	
		备注/Remark		单位/Units: mm	

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------