






300V 12A 26-14AWG 1.5mm²
Poles: 2-16P
Pitch: 5.00mm(.197")

Materials
Housing: PA66(UL 94V-0)
Wire Cage: Brass,Nickel plated
Solder Pin: Brass,Tin Plated
Screw: M3,Steel,Zinc Plated
Torque: 0.5N.m

/Designed by		绘图/Drawing by		审核/Checked by		批准/Approved by		未注公差 General Tolerance		
 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD				图名/Title		文件编号/File No.		x. 0.2 x." 2°		
				XY127S-5.0		QJ/XYT-2239400		.x 0.1 .x° ±1°		
								.xx 0.05 .xx° 0.5°		
				备注 /Remark				页序/Sheet		.xxx 0.01
		单位/Units: mm								