




序号/RevNo.	名称 /Title	文件编号 /File No.
1	XY128A 塑件	QJ/XYT-2140101
2	XY128铜方块	QJ/XYT-2137203
3	XY128R-A端子	QJ/XYT-2140301
4	XY128一字螺丝 (与XY103一字螺丝共用)	QJ/XYT-2140104



300V 15A 24-12AWG 2.5mm²

Poles: 2P/3P-24P

Pitch: 5.0mm(.197")

Materials

Housing: PA66(UL 94V-0)

Wire Cage: Brass,Nickel Plated

Solder Pin: Brass,Tin Plated

Screw: M2.5,Steel,Zinc Plated

Torque: 0.4N.m

设计/Designed by	绘图 /Drawing by	审核 /Checked by	批准 /Approved by	未注公差 General Tolerance				
 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD			图 名 /Title		文件编号 /File No. QJ/XYT-2240300		X, ± 0.2	X", ± 2"
							.X ± 0.1	.X" ± 1"
			XY128RA-5.0		页 序 /Sheet		.XX ± 0.05	.XX" ± 0.5"
							.XXX ± 0.01	
备 注 /Remark				单 位 /Units: mm				

序号 /RevNo.	更改记录 /Revision note	签名 /Signature	日期 /Date
------------	---------------------	---------------	----------