



序号 /RevNo.	名称 /Title	文件编号 /File No.
1	XY128 一字螺丝	QJ/XYT-2140104
2	XY128 铜方块	QJ/XYT-2140102
3	XY128R-B端子	QJ/XYT-2140601
4	XY128B 塑件	QJ/XYT-2140202



300V 15A 24-12AWG 2.5mm²
Poles: 2P&3P-24P
Pitch: 7.5mm(.295")

Materials

Housing: PA66(UL 94V-0)
Wire Cage: Brass,Nickel Plated
Solder Pin: Brass, Tin Plated
Screw: M2.5,Steel(A3),Zinc Plated
Torque: 0.4N.m

序号 RevNo.	更改记录 Revision note	签名 Signature	日期 Date	 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD				
				设计 Designed by	绘图 Drawing by	审核 Checked by	批准 Approved by	未注公差 General Tolerance
				图名 Title		文件编号 File No.		
				XY128R-B		QJ/XYT-2240600		
				产品图		页序 Sheet		
备注 Remark				单位 Units		mm		
				.xxx ± 0.01		± 0.2 ± 0.1 ± 0.05 ± 0.01	± 2° ± 1° ± 0.5°	