






序号 /RevNo.	名称 /Title	文件编号 /File No.
1	XY128A 塑件	QJ/XYT-2140101
2	XY128 铜方块	QJ/XYT-2140102
3	XY128V-A 端子	QJ/XYT-2140103
4	XY103 螺丝	QJ/XYT-2140104

300V 15A 24-12AWG 2.5mm²

Poles: 2P&3P-24P

Pitch: 5.0mm

Materials

Housing: PA66(UL 94V-0)

Wire Cage: Brass,Nickel Plated

Solder Pin: Brass,Tin Plated

Screw: M2.5,Steel(A3),Zinc Plated

Torque: 0.4N.m

设计 /Designed by	绘图 /Drawing by	审核 /Checked by	批准 /Approved by	未注公差 General Tolerance			
 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD				x	± 0.2	x ⁻	± 2°
				.x	± 0.1	.x ⁻	± 1°
				.xx	± 0.05	.xx ⁻	± 0.5°
				.xxx	± 0.01		
图名 /Title XY128VA-5.0 产品图				文件编号 /File No. QJ/XYT-2240100			
备注 /Remark				页序 /Sheet			
				单位 /Units: mm			

序号 /RevNo.	更改记录 /Revision note	签名 /Signature	日期 /Date
------------	---------------------	---------------	----------