




序号/RevNo.	名称 /Title	文件编号 /File No.
1	XY103 螺丝	QJ/XYT-2140104
2	XY128 铜方块	QJ/XYT-2140102
3	XY128V-A 端子	QJ/XYT-2140103
4	XY128B 塑件	QJ/XYT-2140202



300V 15A 24-12AWG 2.5mm²
Poles: 2P&3P-24P
Pitch: 7.5mm(.295")

Materials

Housing: PA66(UL 94V-0)

Wire Cage: Brass,Nickel Plated

Solder Pin: Brass,Tin Plated

Screw: M2.5,Steel(A3),Zinc Plated

Torque: 0.4N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD				x	± 0.2	x"	± 2"
				.x	± 0.1	.x"	± 1"
				.xx	± 0.05	.xx"	± 0.5"
				.xxx	± 0.01		
图名/Title XY128VB-7.5 产品图				文件编号/File No. QJ/XYT-2240500			
备注/Remark				页序/Sheet			
				单位/Units: mm			

序号/RevNo.	更改记录 /Revision note	签名 /Signature	日期 /Date
-----------	---------------------	---------------	----------