




序号 /revNo.	名称 /title	文件编号 /file No.
1	XY129 螺丝	QJ/XYT-2141101
2	XY129 铜方块	QJ/XYT-2141102
3	XY129R(B) 端子	QJ/XYT-2141901
4	XY129V 塑件	QJ/XYT-2141104



300V 20A 26-12AWG 2. 5mm²
Poles: 2P&3P-24P
Pitch: 5.0mm(.197")

Materials

Housing: PA66(UL 94V-0)
Solder Pin: Brass, Tin Plated
Wire Cage: Brass, Nickel Plated
Screw: M3, Steel(A3), Zinc Plated
Torque: 0.5N.m

设计 /Designed by	绘图 /Drawing by	审核 /Checked by	批准 /Approved by	未注公差 General Tolerance	
 新莱亚电子 XINLAIVA ELECTRONIC CO.,LTD		图名 /title	文件编号 /file No.	X. ±0.2	X. ±2°
		XY129RB-5.0	QJ/XYT-2241900	.X ±0.1	.X ±1°
		备注 /remark	页序 /sheet	.xx ±0.05	.xx ±0.5°
				.xxx ±0.01	
				单位 /units: mm	