




序号/RevNo.	名称/Title	文件编号/File No.
1	XY129 螺丝	QJ/XYT-2141101
2	XY129 铜方块	QJ/XYT-2141102
3	XY129R(B) 端子	QJ/XYT-2141901
4	XY129V 塑件	QJ/XYT-2141202



300V 20A 26-12AWG 2.5mm²

Poles: 2P&3P-24P

Pitch: 7.5mm

Materials


Housing: PA66(UL 94V-0)

Solder Pin: Brass,Tin Plated

Wire Cage: Brass,Nickel Plated

Screw: M3,Steel(A3),Zinc Plated

Torque: 0.5N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
 新莱亚电子 XINLAIYA ELECTRONIC CO., LTD				x.	±0.2	x."	±2°
				.x	±0.1	.x"	±1°
				.xx	±0.05	.xx"	±0.5°
				.xxx	±0.01		
图名/Title				文件编号/File No.			
产品图				页序/Sheet			
备注/Remark				单位/Units: mm			

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------