



序号/RevNo.	名称/Title	文件编号/File No.
1	XY129 螺丝	QJ/XYT-2141101
2	XY129 铜方块	QJ/XYT-2141102
3	XY129V-B 端子	QJ/XYT-2141301
4	XY129V 塑件7.5	QJ/XYT-2141501



300V 20A 26-12AWG 2.5mm²
Poles: 2P&3P-24P
Pitch: 7.5mm

Materials

Housing: PA66(UL 94V-0)
Wire Cage: Brass, Nickel Plated
Solder Pin: Brass, Tin Plated
Screw: M3, Steel (A3), Zinc Plated
Torque: 0.5N. m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
				X. ±0.2	X. ° ±0°
	图名/Title	文件编号/File No.		.X ±0.1	.X° ±1°
	XY129VB-7.5	QJ/XYT-2241500		.XX ±0.05	.XX° ±0.5°
	产品图	页序/Sheet		.XXX ±0.01	
备注/Remark				单位/Unit: mm	

