




序号/RevNo.	名称/Title	文件编号/File No.
1	XY130 螺丝	QJ/XYT-2142101
2	XY130 铜方块	
3	XY130 端子	QJ/XYT-D100500
4	XY130 塑件	QJ/XYT-2142104



300V 30A 26-10AWG 4.0mm²
Poles: 2P&3P-24P
Pitch: 9.5mm (.375")

Materials
Housing: PA66 (UL 94V-0)
Solder Pin: Brass, Tin Plated
Wire Cage: Brass, Nickel Plated
Screw: M3, Steel (A3), Zinc Plated
Torque: 0.5N.m

设计/Designed by		绘图/Drawing by		审核/Checked by		批准/Approved by		备注/Remark			
图名/Title		文件编号/File No.		XY130-9.5		QJ/XYT-2242100					
产品图		页序/Sheet									
单位/Unit(s)		mm									

新莱亚电子

XINLAIYA ELECTRONIC CO., LTD

序号/RevNo.

更改记录/Revision note

签名/Signature

日期/Date