




序号/RevNo.	名称/Title	文件编号/File No.
1	XY135 螺丝	QJ/XYT-2143101
2	XY135 方块	QJ/XYT-2143102
3	XY135 端子	QJ/XYT-2143103
4	XY135 塑件	QJ/XYT-2143104



300V 52A 20-6AWG 10.0mm²
Poles: 2P. 3P-24P
Pitch: 10.16mm(.400")

Materials

Housing: PA66 (UL 94V-0)
Solder Pin: Brass, Tin Plated
Screw: M4.5, Steel (A3), Zinc Plated
Torque: 1.2N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
X 新莱亚电子 XINLAIYA ELECTRONIC CO., LTD		图名/Title	文件编号/File No.		x. ±0.2	x. ° ±2°	
		XY135 产 品 图	QJ/XYT-2243100	.x ±0.1	.x° ±1°		
				.xx ±0.05	.xx° ±0.5°		
				.xxx ±0.01			
备注 /Remark				单位/Units: mm			