




序号/RevNo.	名称/Title	文件编号/File No.
1	XY135 螺丝	QJ/XYT-2143101
2	XY135 方块	QJ/XYT-2143102
3	XY136 端子	QJ/XYT-2143103
4	XY136 塑件	QJ/XYT-2143105



300V 52A 20-6AWG 10.0mm²
Poles: 1P-24P
Pitch: 10.16mm(.400")
Materials
Housing: PA66(UL 94V-0)
Solder Pin: Brass,Tin Plated
Screw: M4.5,Steel,Zinc Plated
Torque: 1.2N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
X 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD				x.	±0.2	x."	±2°
				.x	±0.1	.x°	±1°
				.xx	±0.05	.xx°	±0.5°
				.xxx	±0.01		
图名/Title		文件编号/File No.					
XY136-1P							
页序/Sheet							
备注/Remark		QJ/XYT-2243200		单位/Units: mm			

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------