


序号/RevNo.	名称/Title	文件编号/File No.
1	XY305V端子	QJ/XYT-2126101
2	XY166塑件	QJ/XYT-2122101
3	XY305簧片	QJ/XYT-2126102
4	XY166螺丝	QJ/XYT-2126103



300V 15A 22-12AWG 2.5mm²
Poles: 2P,3P-12P
Pitch: 5.0mm(.197")

Material
Housing: PA66(UL 94V-0)
Wire guard: Stainless Steel
Solder Pin: Brass,Tin Plated
Screw: M2.5 steel,Zinc Plated
Torque: 0.4N.m

设计/Designed by		绘图/Drawing by		审核/Checked by		批准/Approved by		未注公差 General Tolerance	
								x.	± 0.2
								.x	± 0.1
								.xx	± 0.05
								.xxx	± 0.01
								x."	± 2"
								.x"	± 1"
								.xx"	± 0.5"
								单位/Units: mm	

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------

X 新莱亚电子
XINLAIYA ELECTRONIC CO.,LTD

图名/Title
XY166 产品图

文件编号/File No.
QJ/XYT-2222100

备注/Remark

页序/Sheet