


序号/RevNo.	名称/Title	文件编号/File No.
1	XY300弹片	QJ/XYT-2124102
2	XY300R端子	QJ/XYT-2124301
3	XY300螺丝	QJ/XYT-2124103
4	XY300R-A塑件	QJ/XYT-2124302



300V 10A 22-14AWG 2.5mm²
Poles: 2P&3P-24P
Pitch: 5.0mm(.197")

Materials


Housing: PBT(UL 94-0)

Wire Protector: Stainless Steel

Solder Pin: Brass,Tin Plated

Screw: M3,Steel(A3),Zinc Plated

Torque: 0.5N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
 新莱亚电子 XINLAIYA ELECTRONIC CO., LTD				x.	±0.2	x."	±2°
				.x	±0.1	.x"	±1°
				.xx	±0.05	.xx"	±0.5°
				.xxx	±0.01		
图名/Title XY300RA-5.0 产品图				文件编号/File No. QJ/XYT-2224300			
备注/Remark				页序/Sheet			
				单位/Units: mm			

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------