



序号/Rev.No.	名称/Title	文件编号/File No.
1	XY301V 端子	QJ/XYT-2127103
2	XY301 簧片	QJ/XYT-2225101
3	XY301 "+" 螺丝	QJ/XYT-2125104
4	XY301VA 塑件	QJ/XYT-2225102



300V 15A 22-14AWG 1.5mm²
Poles: 3P
Pitch: 5.0mm

Materials

Housing: PBT (UL 94V-0)
Wire Protector: Stainless Steel
Solder Pin: Brass, Tin Plated
Screw: M2.5, Steel (A3), Zinc Plated
Torque: 0.4N.m



序号/Rev.No.	更改记录/Revision note	签名/Signature	日期/Date
------------	--------------------	--------------	---------

设计/Designed by		绘图/Drawing by		审核/Checked by		批准/Approved by		未注公差 General Tolerances	
 新莱亚电子 XINLAIYA ELECTRONIC CO., LTD		图名/Title		文件编号/File No.		XY301VA+十字螺丝		QJ/XYT-2225100	
备注/Remark		产品图		页序/Sheet		.xxx ±0.01		单位/Unit: mm	