




序号/RevNo.	名称/Title	文件编号/File No.
1	XY301V 端子	QJ/XYT-2127103
2	XY301 簧片	QJ/XYT-2225101
3	XY301 螺丝	QJ/XYT-2125104
4	XY301V 塑件	QJ/XYT-2225102



300V 15A 22-14AWG 1.5mm²
Poles: 2P&3P-24P
Pitch: 5.0mm

Materials

Housing: PBT(UL 94V-0)
Wire Protector: Stainless Steel
Solder Pin: Brass, Tin Plated
Screw: M2.5, Steel(A3), Zinc Plated
Torque: 0.4N.m

PCB

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
				X, ±0.2	X°, ±2°
				.X ±0.1	.X° ±1°
				.XX ±0.05	.XX° ±0.5°
				.xxx ±0.01	
单位/Units: mm					

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date

图名/Title	文件编号/File No.
XY301V-A	QJ/XYT-2225100
产品图	页序/Sheet
备注/Remark	



新莱亚电子
XINLAIYA ELECTRONIC CO.,LTD