




序号/RevNo.	名称/Title	文件编号/File No.
1	XY302 螺丝	QJ/XYT-2148101
2	XY302 铜方块	QJ/XYT-2148102
3	XY302R 端子	QJ/XYT-2148201
4	XY302 塑件	QJ/XYT-2148103



150V 10A 26-16AWG 1.0mm²
Poles: 2P&3P-24P
Pitch: 3.5mm (.138")

Materials
Housing: PA66 (UL 94V-0)
Solder Pin: Brass, Tin Plated
Wire Cage: Brass, Nickel Plated
Screw: M2, Steel (A3), Zinc Plated
Torque: 0.2N.m

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
图名/Title		文件编号/File No.	X. ° ±0.2		X. ° ±0.2
XY302R-3.5		QJ/XYT-2248200	.X ±0.1		.X° ±1°
页序/Sheet			.XX ±0.05		.XX° ±0.5°
备注/Remark			.XXX ±0.01		
			单位/Unit: mm		



XINLEIYA ELECTRONIC CO., LTD