




序号/RevNo.	名称/Title	文件编号/File No.
1	XY302 螺丝	QJ/XYT-2148101
2	XY302 铜方块	QJ/XYT-2148102
3	XY302V 端子	QJ/XYT-2148104
4	XY302 塑件	QJ/XYT-2148103



150V 10A 26-16AWG 1.0mm²
Poles: 2P&3P-24P
Pitch: 3.5mm(.138")

Materials

Housing: PA66 (UL 94V-0)

Solder Pin: Brass, Tin Plated

Wire Cage: Brass, Nickel Plated

Screw: M2, Steel (A3), Zinc Plated

Torque: 0.2N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
				x.	±0.2	x."	±2°
				.x	±0.1	.x°	±1°
				.xx	±0.05	.xx°	±0.5°
				.xxx	±0.01		
图名/Title XY302V-3.5 产品图				文件编号/File No. QJ/XYT-2248100			
备注/Remark				页序/Sheet 单位/Units: mm			

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------