




序号/RevNo.	名称 /Title	文件编号/File No.
1	XY303 一字螺丝 (与XY302一字螺丝共用)	QJ/XYT-2148101
2	XY303 铜方块 (与XY302铜方块共用)	QJ/XYT-2148102
3	XY303R 端子 (与XY302R端子共用)	QJ/XYT-2148201
4	XY303 塑件	QJ/XYT-2149101



300V 10A 26-16AWG 1.0mm²
Poles: 2P&3P-24P
Pitch: 3.81mm(.150")

Materials
Housing: PA66(UL 94V-0)
Wire Cage: Brass,Nickel Plated
Solder Pin: Brass,Tin Plated
Screw: M2,Steel(A3),Zinc Plated
Torque: 0.2N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD				x. ±0.2	x." ±2°
				.x ±0.1	.x" ±1°
				.xx ±0.05	.xx" ±0.5°
				.xxx ±0.01	
图名/Title				文件编号/File No.	
XY303R 产品图				QJ/XYT-2249200	
备注/Remark				页序/Sheet	
				单位/Units:	mm