




序号/RevNo.	名称 /Title	文件编号 /File No.
1	XY304 螺丝	QJ/XYT-2150101
2	XY304 铜方块	QJ/XYT-2150102
3	XY304V 端子	QJ/XYT-2150103
4	XY304 A 塑件 5.0	QJ/XYT-2150104



300V 12A 26-14AWG 1.5mm²

Poles: 2P&3P-24P

Pitch: 5.0mm

Materials


Housing: PA66(UL 94V-0)

Solder Pin: Brass,Tin Plated

Wire Cage: Brass,Nickel Plated

Screw: M3.0,Steel(A3),Zinc Plated

Torque: 0.5N.m

设计 /Designed by	绘图 /Drawing by	审核 /Checked by	批准 /Approved by	未注公差 General Tolerance			
 XY304V-5.0 产品图				x, ± 0.2	x', ± 2"		
				.x, ± 0.1	.x', ± 1"		
				.xx, ± 0.05	.xx', ± 0.5"		
				.xxx, ± 0.01			
				图名 /Title	文件编号 /File No.	页序 /Sheet	单位 /Units: mm
				备注 /Remark			