




序号/RevNo.	名称/Title	文件编号/File No.
1	XY307端子	QJ/XYT-2128101
2	XY307弹片 通用XY300	QJ/XYT-2124102
3	XY307螺丝 通用XY300	QJ/XYT-2124103
4	XY307塑件	QJ/XYT-2128102



300V 12A 22-14AWG 2.5mm²
Poles: 2P&3P-24P
Pitch: 5.0mm(.197")

Materials

Housing: PBT (UL 94V-0)
Wire Protector: Stainless steel
Solder Pin: Brass, Tin Plated
Screw: M3, Steel (A3), Zinc Plated
Torque: 0.5N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance	
 新莱亚电子 XINMATA ELECTRONIC CO., LTD		图名/Title	文件编号/File No.	X. ±0.2	X. ° ±0°
		XY307A-5.0	QJ/XYT-2228100	.X ±0.1	.X ° ±1°
		产品图	页序/Sheet	.XX ±0.05	.XX ° ±0.5°
备注/Remark				.XXX ±0.01	
				单位/Unit: mm	