




序号/RevNo.	名称/Title	文件编号/File No.
1	XY636螺丝	
2	XY636方针	
3	XY636端子	
4	XY636-7.62塑件	



Poles: 2P&3P-24P
Pitch: 7.62mm
Voltage Rating: 300V
Current Rating: 30A
Wire range: 26-10AWG 4.0mm²
Housing: PA66 (UL 94V-0)
Wire Cage: Brass1,Nickel Plated
Solder Pin: Brass,Tin Plated
Screw: M3.0,Steel (A3),Zinc Plated
Torque: 0.5N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
 新莱亚电子 XINLAIYA ELECTRONIC CO.,LTD				x.	±0.2	x."	±2°
				.x	±0.1	.x°	±1°
				.xx	±0.05	.xx°	±0.5°
				.xxx	±0.01		
图名/Title 文件编号/File No. XY636-7.62 QJ/XYT-2252200 页序/Sheet				单位/Units: mm			
备注/Remark							

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------