




序号/RevNo.	名称/Title	文件编号/File No.
1	XY636螺丝	
2	XY636方针	
3	XY636端子	
4	XY636-9.25塑件	



Poles: 2P&3P-24P
Pitch: 9.52mm
Voltage Rating: 300V
Current Rating: 30A
Wire range: 26-10AWG 4.0mm²
Housing: PA66 (UL 94V-0)
Wire Cage: Brass, Nickel Plated
Solder Pin: Brass, Tin Plated
Screw: M3.0, Steel, Zinc Plated
Torque: 0.5N.m

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance			
新莱亚电子 XINLAIYA ELECTRONIC CO., LTD		图名/Title		文件编号/File No.			
		XY636-9. 52		QJ/XYT-2252300			
				页序/Sheet			
		备注 /Remark				单位/Units: mm	

序号/RevNo.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------