


# ROCKER SWITCH MODEL MR-5 SERIES

RATING:3A 250VAC  $\mu$  (cURus)




6A 125VAC  $\mu$  (cURus)

3A 250V~ μT100/55 (ENEC15/CQC)

DIELECTRIC VOLTAGE-WITHSTAND:1,500VAC FOR 1 MINUTE

INSULATION RESISTANCE:DC 500V 100MΩ (MIN.)

CONTACT RESISTANCE:20mΩ INITIAL (MAX.)



MOUNTING HOLE

|   | X Cutout Dimension                     | Panel Thickness |
|---|----------------------------------------|-----------------|
| A | .535/13.6 <sup>+0</sup> <sub>-.1</sub> | 0.75~1.25       |
| B | .539/13.7 <sup>+0</sup> <sub>-.1</sub> | 1.25~2.0        |
| C | .543/13.8 <sup>+0</sup> <sub>-.1</sub> | 2.0~2.5         |

NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED:  $\pm .012/0.3$  (in/mm)

| REVISION   | DESCRIPTION | REVISED BY | TOLERANCES |     | ANGLE $\frac{1}{2}^\circ$ |    | UNIT  | mm         | PART NAME | MR5 SPEC DRAWING | DWG NO  |
|------------|-------------|------------|------------|-----|---------------------------|----|-------|------------|-----------|------------------|---------|
|            |             |            | DRAWN BY   | 楊偉韶 | DESIGNED BY               | 蔡劍 | SCALE | 3/1        |           |                  | PART NO |
|            |             |            | CHECKED BY |     | APPROVED BY               |    | DATE  | 2021.06.04 |           |                  |         |
|            |             |            |            |     |                           |    |       |            |           |                  |         |
| 2021.06.04 | 首次出图        | 楊偉韶        |            |     |                           |    |       |            |           |                  |         |