


RATING: 12(4)A 125/250V~ (cURus, ENEC15)

10(4)A 250V~T125/55 (CQC)

DIELECTRIC WITHSTAND VOLTAGE:1500VAC FOR 1 MINUTE

INSULATION RESISTANCE:500VDC 100MΩ (MIN.)

CONTACT RESISTANCE: 20mΩ INITIAL(MAX.)



X(CUTOUT DIMENSION)	Y(CUTOUT DIMENSION)	Z(PANEL THICKNESS)
19.2 ^{+0.15} ₋₀ mm	6.65~6.75mm	0.75~1.25mm
19.4 ^{+0.15} ₋₀ mm	6.65~6.75mm	1.25~2mm
19.8 ^{+0.15} ₋₀ mm	6.65~6.75mm	2~3mm

MODEL NO, SEE NUMBER SYSTEM

REVISION	DESCRIPTION	REVISED BY	TOLERANCES		ANGLE 1/2°			UNIT	mm	PART NAME	MR SPEC DRAWING	DWG NO
 4			DRAWN BY	郭洋	DESIGNED BY	蔡劍	SCALE	2/1				PART NO
 3			CHECKED BY		APPROVED BY		DATE	2013.02.21				
 2												
 1 2013.02.21	依UL61058-1首次出圖	郭洋										