

SPECIFICATION FOR APPROVAL

業務部



TO: TME

1/2


PART NAME	EMI FILTER	YUNPEN SAMPLE NO	FTB-6181
YUNPEN MODEL	YR06A3	SAMPLE DATE	OCT.30.2015
MODEL NO		OUR DRAWING NO	DR-00475

1. PHYSICAL DIMENSIONS:(mm)

SUGGESTED CUTOUT MOUNTING DIMENSIONS OF SOCKET



2. SCHEMATIC:



CX : 0.1uF
CY : 3300pF
L : 2X0.7mH

REPORTED BY	CHECKED BY	APPROVED BY	3	
			2	
			REV. 1	

CK002 30101

YUNPEN ELECTRONIC CO.,LTD

3F., No.32, Zhongxing Rd., Xizhi Dist., New Taipei City 221, Taiwan (R.O.C.)

TEL:(02)2647-1327 FAX:(02)2647-1329 <http://www.yunpen.com.tw>

E-mail: sales@yunpen.com.tw

SPECIFICATION FOR APPROVAL 業務部

TO: TME

2/2

PART NAME	EMI FILTER	YUNPEN SAMPLE NO	FTB-6181
YUNPEN MODEL	YR06A3	SAMPLE DATE	OCT.30.2015
MODEL NO		OUR DRAWING NO	DR-00475

3.ELECTRICAL CHARACTERISTICS:

- 3-1.RATED VOLTAGE125/250VAC
 3-2.RATED CURRENT 6 A
 3-3.OPERATING FREQUENCY 50/60Hz
 3-4.LEAKAGE CURRENT:EACH LINE TO GROUND
 250VAC 50Hz 0.8mA MAX
 3-5.HIPOT RATING.(FOR ONE MINUTE)
 LINE TO LINE 1450VDC
 LINE TO GROUND 1800VAC
 3-6.INSULATION RESISTANCE 250VDC/100MOHM MIN
 3-7.DIRECT CURRENT RESISTANCE 0.15 OHM MAX
 3-8.OPERATING TEMPERATURE -25 TO +85°C

4..SAFETY COMPLIANCE:

UL FILE NO:E134751
 VDE FILE NO:40028561
 CQC FILE NO:12001067993
 CE

REPORTED BY	CHECKED BY	APPROVED BY	3	
			2	
			REV. 1	

YUNPEN ELECTRONIC CO.,LTD

CK002 30101

3F., No.32, Zhongxing Rd., Xizhi Dist., New Taipei City 221, Taiwan (R.O.C.)

TEL:(02)2647-1327 FAX:(02)2647-1329 <http://www.yunpen.com.tw>

E-mail: sales@yunpen.com.tw