

article#	4670002
article description	PRCD-S+ PCE 30mA1.5/1.5m3G1.5H07 St/3WK
description long	Safety extension cord with PRCD-S+ 16A 250V~; I Δ N = 30mA Housing grey /black /red 3m cable H07RN-F 3G1,5mm ² Entry: 1,5m cable with TopTaurus2 safety plug (05721-sr) Outlet: 1,5m cable with solid rubber safety 3-way connector with hinged lid (253622-s) Protection degree: IP44 PRCD-S+ according DIN VDE 0661 DGUV Information 203-006 (former BGI/GUV-I 608) Ready wired, mounted and tested
GTIN (EAN)	9003399321849
country of origin	SI
customs number	85371098
net weight	1.230 kg
packaging quantity	1
minimum order quantity	1

ETIM 9.0	EC000003
Number of poles	3
Rated voltage	230 V
Rated current	16 A
Rated fault current	0.03 A
Mounting method	Adapter plug
Leakage current type	Other
Frequency	50 Hz
Degree of protection (IP)	IP44

