

Cat.5E 24 port shielded patch panel, 19" 1U

NPP-C524-002



Specifications

Dimensions: 483 x 111 x 45 mm

Net weight: 1.7 kg

Features

- Termination: 110-type
- Space saving, high-density 19" panel design
- Designed to mount to any standard 19" rack or cabinet
- 50μ gold-plated contacts
- Black electrostatic powder-coated steel
- Accommodates top, bottom or side cable entry
- Write-on designation label with clear holder on front side
- Rear cover with wire management bar to ensure proper patch cables bend radius and strain relief
- For EIA/TIA T568B/A wiring configuration

Packaging

Q'ty in crtn, pcs	10
Crtn volume, CUM	0.043
Crtn weight, kgs	17.7
Individual package size LxWxH:	50x130x500 mm
Carton size LxWxH:	515x300x280 mm
Country of origin	CN
Barcode	8716309079617
Customs code	8536901000

Certificates

