

Cat.6 24 port patch panel with rear cable management

NPP-C624CM-001



Specifications

Dimensions: 483 x 47 x 86 mm

Net weight: 0.8 kg

Features

- Termination: 110-type
- Space saving, high-density 19" panel design
- Designed to mount to any standard 19" rack or cabinet
- 50μ gold-plated contacts
- Black electrostatic powder-coated steel
- Accommodates top, bottom or side cable entry
- Write-on designation label with clear holder on front side
- Rear cover with wire management bar to ensure proper patch cables bend radius and strain relief
- For EIA/TIA T568B/A wiring configuration

Packaging

Q'ty in crtn, pcs	20
Crtn volume, CUM	0.082
Crtn weight, kgs	27.4
Individual package size LxWxH:	505x125x60 mm
Carton size LxWxH:	520x280x560 mm
Country of origin	CN
Barcode	8716309079563
Customs code	8536901000

Certificates

