

Power cord (C13), 1 m

PC-186-1M



Features

- German Schuko input and C13 output
- Molded plugs with integrated strain relief

Specifications

Length: 1 m

Input plug: Shuko type with ground contact hole and 4.9 mm pins

Output plug: C13

Wires: profile area 0.5 sq.mm, 6 A rating

Packaging

Q'ty in crtn, pcs
Crtn volume, CUM
Crtn weight, kgs
Individual package size LxWxH:
Carton size LxWxH:
Country of origin
Barcode
Customs code

100
0.032
19
270x70x60 mm
400x300x270 mm
CN
8716309129862
8544429090

Certificates

