



# MEDUSA

## WIRELESS KEYBOARD

### PRODUCT FEATURES:

- Dual wireless connectivity 2.4 GHz and BT 5.1 - forget about tangled cables
- Ability to connect up to 3 devices simultaneously and switch between them
- Quiet and smooth key operation, thanks to the X-scissor mechanism
- 21 multifunction keys make every day work easier
- Low profile and appropriate key layout allows long hours of use without fatigue or wrist pain
- Low battery indicator warns you before the power is fully depleted
- Built-in 500 mAh battery - you don't have to worry about replacing batteries while saving the environment
- UV coating on the letters increases their resistance to abrasion
- ON/OFF power switch for safe carrying



### PRODUCT SPECIFICATION:

|                                    |                                                                   |
|------------------------------------|-------------------------------------------------------------------|
| <b>Communication</b>               | Wireless                                                          |
| <b>Interface</b>                   | 2.4 GHz, Bluetooth compatibility                                  |
| <b>Layout</b>                      | US                                                                |
| <b>Key mechanism</b>               | X-Scissors                                                        |
| <b>Illumination</b>                | No                                                                |
| <b>Range</b>                       | 10 m                                                              |
| <b>Number of keys</b>              | 117                                                               |
| <b>Number of multimedia keys</b>   | 21                                                                |
| <b>Supported Operating Systems</b> | Android, Linux, MAC, Windows 8, Windows 10, Windows 7, Windows 11 |
| <b>Power supply</b>                | Built-in battery                                                  |
| <b>Dimensions</b>                  | 428 x 137 x 22 mm                                                 |

