

PPU6-1048-B

PATCH PANEL 48 PORT 1U 19" CAT.6 UTP



PRODUCT FEATURES:

- 48 RJ-45 Cat. 6 Ports – High port density allows efficient management of numerous network connections in a compact 1U unit.
- IDC/LSA Terminals – Enables quick and hassle-free cable termination using industry-standard punch-down connectors.
- Integrated Cable Management Shelf – Reinforced shelf with brackets ensures organized cabling and enhanced installation stability.
- 19" Rack Compatibility & T568A/B Standards – Fully compliant with widely used mounting and wiring standards.
- Durable Metal Construction – Designed for reliability and long-lasting performance in demanding network environments.

PRODUCT SPECIFICATION:

Number of ports	48
Connector type	Equipped
ICT height	1 U
Size	19",
ICT category	Cat. 6
Shielding	No
Equipped with connectors	Yes
Fitting type	IDC/LSA
Material	Metal
Standard	T568A, T568B
Ports identification in the form of numbered fields	Yes
RAL color	RAL9004
Colour	Black
Dimensions	102 x 445 x 44,45 mm
Weight	1,35 kg
Included Accessories	Integrated cable shelf

