

TECHNICAL DATA

Producer	Qoltec
Power	12W
Input voltage	220 ~ 240V
Output voltage	6/12VDC
Type of charging	CC-CV
Output current	1.5A
Charging time	Depending on battery capacity
Connector	Red and black alligator clip clamps
Display	NO
Protection	Against short circuit Against overheating Against open circuit
Protection against inverse polarity	Yes
Cable length	1.70m
Usage	Maintenance-free batteries: AGM GEL STD
OTHER PARAMETERS	
Colour	Black
Material	Polycarbonate (PC)
Operating temperature	-20°C ~ +40°C
Dimensions (D/L x W x H)	50 x 50 x 95 mm
Package	Box
Package contents	1 x Charger 1 x Warranty card
Package depth / length [mm]	55
Package width [mm]	72
Package height [mm]	155
Net weight [kg]	0.128
Gross weight [kg]	0.144
Certificate	CE
Warranty	24 month
EAN code	5901878524238