

TECHNICAL DATA

Producer	Qoltec
Maximum power	390W for PV 12V 780W for PV 24V
Rated voltage	12/24V
Rated current	30A
Maximum PV array open circuit voltage	<100V
MPPT efficiency	95%
Battery type	Compatible with GEL, LiFePO4, Flooded, Li(NiCoMn)o2
Display	LCD
Safety	Short-circuit protection Overheating protection Overload protection Overcharge protection
Usage	Home photovoltaic systems Portable solar kits Solar systems in RVs and caravans Solar installations on boats and yachts Any location requiring efficient and reliable battery charging management
Additional information	Equipped with Maximum Power Point Tracking (MPPT) technology Bluetooth option
IP rating	IP30
Operating temperature	-20°C ~ +55°C
Storage temperature	-30°C do +80°C
OTHER PARAMETERS	
Colour	Grey, Green
Material	ABS, metal
EAN code	5901878536620