

TECHNICAL DATA

Producer	Qoltec
Power	12W
Input voltage	220 – 240V
Output voltage	12VDC
Type of charging	CC-CV
Output current	1A
Charging time	Depending on battery capacity
Connector	Red and black alligator clip clamps
Display	NO
Protection	Short-circuit protection Protection against overheating
Protection against inverse polarity	Yes
Cable length	1.70m
Usage	Maintenance-free batteries: AGM GEL STD
OTHER PARAMETERS	
Colour	Black
Material	Polycarbonate (PC)
Operating temperature	-20°C ~ +40°C
Dimensions (D/L x W x H)	48 x 45 x 75 mm
Package	Box
Package contents	1 x Charger 1 x Warranty card
Package depth / length [mm]	55
Package width [mm]	95
Package height [mm]	125
Net weight [kg]	0.091
Gross weight [kg]	0.108
Certificate	CE
Warranty	24 month
EAN code	5901878524245