


article#	864-6gv
article description	CEE-wall socket (surface outlet) Design 16A 4p 6h IP44 (grey)
description long	CEE-wall socket (surface outlet) Design 16A 4p 6h IP44 (grey) housing material: PC/ABS rated current: 16A number of poles: 4 (3P+PE) clock-position: 6h rated voltage/frequency: 380-415V~ / 50+60Hz contacts: brass nickel plated connection technology: screw terminals color: grey (similar to RAL 7035) wall-/surface-mounting hinged lid with inscription field (optional: key lock) IP protection class: IP44
GTIN (EAN)	9003399570599
country of origin	AT
customs number	85366990
net weight	0.294 kg
packaging quantity	6
minimum order quantity	6

ETIM 9.0	EC001321
Model	Surface mounted
IEC-amperage	16 A
Number of poles	4
Voltage according to EN 60309-2	380-415 V (50+60 Hz) red
Clock hour position	6 h
Identification colour	Red
Degree of protection (IP)	IP44
Connection system	Screw terminal
Material	Plastic
Contact material	CuZn
Surface treatment contacts	Nickel-plated

a	90 mm
b	90 mm
c	73 mm
d	73 mm
e	47 mm
f	48 mm
g	25 mm
wire flexible	1-2x2,5 mm ²
wire solid	1-2x4 mm ²
contact screws	100 Ncm
dismantling length	50 mm
stripping length	10-12 mm
ambient temperature	-25 – 40 °C
temperature resistance	-25 – 80 °C



<https://www.pcelectric.at/shop/en/?func=detail&artnr=864-6gv>