



article#	895-6gv
article description	CEE-flush socket outlet incl. flush socket Design 32A 5p 6h IP44 (grey)
description long	CEE-flush socket outlet incl. flush socket Design 32A 5p 6h IP44 (grey) housing material: PC/ABS rated current: 32A number of poles: 5 (3P+N+PE) clock-position: 6h rated voltage/frequency: 200/346V~ - 240/415V~ / 50+60Hz contacts: brass nickel plated connection technology: screw terminals color: grey (similar to RAL 7035) flush mounting (incl. Flush socket) hinged lid with inscription field (optional: key lock) IP protection class: IP44
GTIN (EAN)	9003399673801
country of origin	AT
customs number	85366990
net weight	0.391 kg
packaging quantity	6
minimum order quantity	6

ETIM 9.0	EC001321
Model	Flush-mounted
IEC-amperage	32 A
Number of poles	5
Voltage according to EN 60309-2	400 V (50+60 Hz) red
Clock hour position	6 h
Identification colour	Red
Degree of protection (IP)	IP44
Connection system	Screwed terminal
Material	Plastic
Contact material	CuZn
Surface treatment contacts	Nickel-plated

a	90 mm
b	90 mm
c	92 mm
d	115 mm
e	64 mm
f	35 mm
wire flexible	2,5-2x6 mm ²
wire solid	2,5-2x10 mm ²
contact screws	110 Ncm
dismantling length	50 mm
stripping length	12-14 mm
ambient temperature	-25 – 40 °C
temperature resistance	-25 – 80 °C



<https://www.pcelectric.at/shop/en/?func=detail&artnr=895-6gv>