

Art 650G ESD CLEAN FINGER COTS

GENERAL

- Material : 100% nature latex
- Color: Pink, Cream

PHYSICAL

Sizes	S	M	L	XL
Length (mm)	70 +/-5	70 +/-5	70 +/-5	70 +/-5
Weight(g)	0,41	0.46	0.52	0,58
Flat Width (mm)	24	28	30	34
Thickness(mm)	0.09	0.09	0.09	0,09



ESD

Item	Specification	Standard
SurfaceResistivity(Ω/cm^2)	$\leq 10^{11}$	ANSI/ESD-STM11.11 ASTM D257
DecayTime(seconds)	< 3.0	ANSI/ESD-STM11.11 ASTM D257
StaticCharge(volts)	≤ 50	ANSI/ESD-STM11.11 ASTM D257
TriboelectricCharge(Volts)	150	ANSI/ESD-STM11.11 ASTM D257

APPLICATIONS

- Good for use in Clean Room
- ESD safe.
- Nitrogen flushed and vacuum packaged to keep clean.
- Meets Mil. Std. 81705 B on static decay test.
- Elongation > 600%
- Tensile strength > 200kg per square meter.

PACKING

- SIZE S: 1440pcs 660gr polybag
- SIZE M: 1440pcs 768gr polybag
- SIZE L: 1440pcs 799gr polybag
- SIZE XL: 1440pcs 954gr polybag

The data shown above are intended only as a general indication of the standard production values. They do not refer to specific production lots. The document has no legal value.
EUROSAFT srl