




Type Designation	4106
Designation IEC	LR6
System	Zn-MnO ₂ (Alkaline)
Shelf Life (Coding)*	10 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	2800 (discharge with high-resistance)
Permissible Temperature Range	- 10 °C ... 50 °C
Weight, approx. [g]	23,2
Volume [ccm]	7.5

Dimensions [mm]

min: max:

Ø	13.7	14.5
A	-	50.5
B	49.5	-
C	7.0	-
E	-	0.5
F	-	5.5
G	1.0	-

Typical Capacities (at 20°C):


Discharge Type	Load	End Voltage[V]	0.9
1H/D,7D/W	100 mA	Time [h]	25,0
Digital Audio		Capacity [Ah]	2,48
		Energy [Wh]	3,0
Discharge Type	Load	End Voltage[V]	1.0
1H /8H/D,7D/W	50 mA	Time [h]	49,5
Radio / Clock / Remote Control		Capacity [Ah]	2,47
		Energy [Wh]	3,14
Discharge Type	Load	End Voltage[V]	0.9
1H/D,7D/W	250 mA	Time [h]	8,5
Toy, non motorized		Capacity [Ah]	2,15
		Energy [Wh]	2,5

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

* In consideration of typical loss of capacity at storage and application.