


armac-

UPS ARMAC

OFFICE ON-LINE PFI 3000VA
DUST FREE



PRODUCT SPECIFICATION:

UPS topology	On-line (VFI)
Power	3 000 W
PowerFactor	1
Device efficiency	95,5 %
Type of casing	Tower
Number of outlets	8
Outlet type	IEC C13
Battery quantity	6
Connectors	RS-232, USB Type-B
Battery pack connector	Yes
Battery capacity	9 Ah
Battery type	Lead acid VRLA AGM
Battery voltage	12 V
Recharge time	6 h
Input voltage	230 V
Input voltage range	from 110 up to 300 V
Input frequency range	from 40 up to 70 Hz
Output voltage	230 V
Output acceptable voltage range	from 208 up to 240 V
Output frequency	60 Hz
Automatic Voltage Regulation (AVR)	Yes
Waveform type	Full sine wave
AC/DC Transfer time	from 0 up to 0 ms
Cold start	Yes
Protections	Interference filter, Overload protection, Short circuit protection, Surge protection
Noise level	50 dB
Colour	Black
Software	PowerManager II
Supported Operating Systems	Linux, Unix, Windows 7, Windows 7 64bit, Windows 10, Windows 10 64bit, Windows 11
Weatherproof rating	IP20
Dimensions	418 x 190 x 322 mm
Weight	27 kg

EAN-13: 5901969446982
CAT. NO: T/3000I/PFI/DF

Despite all efforts, the manufacturer / distributor / seller does not guarantee that the published technical data, photos and descriptions do not contain any deficiencies or mistakes. The above catalogue is for information purposes and does not constitute an offer within the meaning of the Civil Code.