




SCHEMATIC




General specifications

Circuit	: ON-ON(2P2T)
Rating	: D.C. 6V 0.3A
Contact R.[max]	: 30m Ω
Insulation R.[min]	: D.C. 500V 100M Ω
Withstand VOL.	: A.C. 500V 1minute
Timing	: Non Shorting
Operating force	: 200 $\pm$ 100g
Life cycle[max]	: 10,000 CYCLES

MATERIAL SPECIFICATIONS

ITEM	PART NAME	MATERIAL	FINISH
1	KNOB	NYLON	NA
2	COVER	SUS	WASHING
3	CASE	Brass Strip/Nylon+Glass	Black/Ag Plated
4	CONTACT	0.1mm PBS C5210R-EH	Ag Clad

P.C.B. HOLE DETAIL




亮群股份有限公司
LIGHT COUNTRY CO., LTD
TEL: 886-2-22253580
FAX: 886-2-22253827
<http://www.lightcountry.com>

比例 SCALE	1 : 8
單位 DIMENSION	m m
DO NOT SCALE DRAWING TOLERANCES UNLESS OTHERWISE	
UP TO 10	± 0.3
ABOVE 10 TO 100	± 0.5
ABOVE 100	± 0.8
ANGULAR DIMENSIONS	$\pm 5^{\circ}$

品名 TITLE MINI SLIDE SWITCH

型號 MODEL MSS-2235

繪圖 DRAWN MKL 核准 APPROVED HSH



版次 REVISION

A

日期 DATE

2008/11/03