







General specifications

Circuit	: ON-ON(2P2T)
Rating	: D.C. 6V 0.3A
Contact R.[max]	: D.C. 5V 1A 70m Ω
Insulation R.[min]	: D.C. 500V 100M Ω
Withstand VOL.	: A.C. 500V 1minute
Timing	: Non Shorting
Operating force	: 200 ± 100 g
Life cycle[max]	: 5,000 CYCLES

SCHEMATIC



P.C.B. HOLE DETAIL



Light Country Co., Ltd.

比例 SCALE 1 : 8

單位 DIMENSION m m

DO NOT SCALE DRAWING
TOLERANCES UNLESS OTHERWISE

UP TO 10 ± 0.3

ABOVE 10 TO 100 ± 0.5

ABOVE 100 ± 0.8

ANGULAR DIMENSIONS $\pm 5^\circ$

品名 TITLE

MINI SLIDE SWITCH

型號 MODEL

MSS-2245

繪圖
DRAWN

MKL 2006/05/26

核准
APPROVED

HSH 2006/05/26



版次
REVISION

A

日期
DATE

2006/05/26