







General specifications

Circuit	: ON-ON-ON(2P3T)
Rating	: D.C. 6V 0.3A
Contact R.[max]	: D.C. 5V 1A 30m Ω
Insulation R.[min]	: D.C. 500V 100M Ω
Withstand VOL.	: A.C. 500V 1minute
Timing	: Non Shorting
Operating force	: 250 ± 100 g
Life cycle[max]	: 10,000 CYCLES

SCHEMATIC



P.C.B. HOLE DETAIL



亮群股份有限公司
LIGHT COUNTRY CO., LTD
TEL:886-2-22253580
FAX:886-2-22253827
<http://www.lightcountry.com>

比例 SCALE	1 : 8
單位 DIMENSION	m m
DO NOT SCALE DRAWING TOLERANCES UNLESS OTHERWISE	
UP TO 10	± 0.3
ABOVE 10 TO 100	± 0.5
ABOVE 100	± 0.8
ANGULAR DIMENSIONS	$\pm 5^\circ$

品名 TITLE	MINI SLIDE SWITCH			
型號 MODEL	MSS-2336			
繪圖 DRAWN	MKL 2006/05/26	核准 APPROVED	HSH 2006/05/26	
版次 REVISION	A	日期 DATE	2006/05/26	