



	1	2	3	4	5	6	7	8																								
A	<table><tr><td>Raw Material</td><td>PA66 SILICONE COPPER ALLOY</td></tr><tr><td>Flame-resistant rating</td><td>UL94 V-2</td></tr><tr><td>Level of protection</td><td>IP68</td></tr><tr><td>Voltage rating/Current rating</td><td>450 V / 24 A</td></tr><tr><td>Withstanding voltage</td><td>2500 V</td></tr><tr><td>Cable gague</td><td>0.5~2.5mm²</td></tr><tr><td>Operating temperature</td><td>-40~105 ℃</td></tr></table>		Raw Material	PA66 SILICONE COPPER ALLOY	Flame-resistant rating	UL94 V-2	Level of protection	IP68	Voltage rating/Current rating	450 V / 24 A	Withstanding voltage	2500 V	Cable gague	0.5~2.5mm²	Operating temperature	-40~105 ℃	2 PIN  															
Raw Material	PA66 SILICONE COPPER ALLOY																															
Flame-resistant rating	UL94 V-2																															
Level of protection	IP68																															
Voltage rating/Current rating	450 V / 24 A																															
Withstanding voltage	2500 V																															
Cable gague	0.5~2.5mm²																															
Operating temperature	-40~105 ℃																															
B																																
C																																
D	<table><tr><td>Type</td><td>Rubbers Diameter(d) ±0.35mm</td><td>Outer Cable Diameter</td></tr><tr><td>A</td><td>φ 14.5 mm</td><td>φ 10~14 mm</td></tr><tr><td>B</td><td>φ 12 mm</td><td>φ 9~12 mm</td></tr><tr><td>C</td><td>φ 8.5 mm</td><td>φ 5~9 mm</td></tr></table>								Type	Rubbers Diameter(d) ±0.35mm	Outer Cable Diameter	A	φ 14.5 mm	φ 10~14 mm	B	φ 12 mm	φ 9~12 mm	C	φ 8.5 mm	φ 5~9 mm												
Type	Rubbers Diameter(d) ±0.35mm	Outer Cable Diameter																														
A	φ 14.5 mm	φ 10~14 mm																														
B	φ 12 mm	φ 9~12 mm																														
C	φ 8.5 mm	φ 5~9 mm																														
E																																
F	Rubbers D ameter  																															
G																																
H	<table><tr><td colspan="2"> RoHS Compliant </td><td colspan="2"> HSM玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD. </td></tr><tr><td>APPD. 核准</td><td></td><td>TOLERANCE X. ±0.35 X° ±3° X.X ±0.20 X.X° ±2° X.XX ±0.10 X.XX° ±1° X.XXX ±0.05</td><td>PART NAME 品名 M25 TYPE WATERPROOF CONNECTOR 2PIN WATERPROOF GRADE:IP68 24A 450V T/L:108MM(REF.) BODY MATERIAL:PA66 UL94V-2 BLACK COLOR ROHS</td></tr><tr><td>DWG. 製圖</td><td>Hedy</td><td>SCALE 比例 參考</td><td></td></tr><tr><td>DATE 制表日 2025/06/20</td><td></td><td>UNIT 單位 MM</td><td></td></tr><tr><td></td><td></td><td>PAGE 張數 1 / 1</td><td></td></tr><tr><td></td><td></td><td>REV. 版次 A</td><td>PART NO. 料號 C9455-02AB(A,B,C)000R</td></tr></table>								RoHS Compliant		HSM玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.		APPD. 核准		TOLERANCE X. ±0.35 X° ±3° X.X ±0.20 X.X° ±2° X.XX ±0.10 X.XX° ±1° X.XXX ±0.05	PART NAME 品名 M25 TYPE WATERPROOF CONNECTOR 2PIN WATERPROOF GRADE:IP68 24A 450V T/L:108MM(REF.) BODY MATERIAL:PA66 UL94V-2 BLACK COLOR ROHS	DWG. 製圖	Hedy	SCALE 比例 參考		DATE 制表日 2025/06/20		UNIT 單位 MM				PAGE 張數 1 / 1				REV. 版次 A	PART NO. 料號 C9455-02AB(A,B,C)000R
RoHS Compliant		HSM玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.																														
APPD. 核准		TOLERANCE X. ±0.35 X° ±3° X.X ±0.20 X.X° ±2° X.XX ±0.10 X.XX° ±1° X.XXX ±0.05	PART NAME 品名 M25 TYPE WATERPROOF CONNECTOR 2PIN WATERPROOF GRADE:IP68 24A 450V T/L:108MM(REF.) BODY MATERIAL:PA66 UL94V-2 BLACK COLOR ROHS																													
DWG. 製圖	Hedy	SCALE 比例 參考																														
DATE 制表日 2025/06/20		UNIT 單位 MM																														
		PAGE 張數 1 / 1																														
		REV. 版次 A	PART NO. 料號 C9455-02AB(A,B,C)000R																													
	1	2	3	4	5	6	7	8																								