

CONDUCTIVE BOXES (new organization system for EGB laboratories)

ALU RAILS (diverting)
Spiral cable and wrist strap included

Plate **8190015**

Plate **8190016**

Clip **2423037**

Hooks 5 piece-Set **8190017**

8169093 (100 cm)

8169092 (50 cm)

Art. No.	8140027	8140028
Outside dim.	160 x 210 x 82	240 x 210 x 82
Inside dim.	126 x 178 x 79	208 x 178 x 79
Colour	●	●

CONDUCTIVE BOXES + SUBDIVISIONS

Art. No. **2422798**Designation **A 4-1-6-10**

Base area 175 x 100

Top edge 205 x 125

Height inside 34 mm

Colour ●

Art. No. **2422852**Designation **A 4-2-6-10**

Base area 190 x 120

Height inside 50 mm

Colour ●

Art. No. **2422858**Designation **A 4-3-6-10**

Base area 210 x 150

Top edge 260 x 200

Height inside 40 mm Colour ●

Art. No. (a) **2422885**Designation **A 4-4 N-6-10**Art. No. (b) **2430850**Designation **A 4-70 N-6-10**

Outside dim. 260 x 165

Top edge (a) 45 (b) 70 Colour ●

PORTABLE RACK, CHROME-PLATED FOR 8 OR 10 TRAYS

Art. No. **2432472**Designation **A 4-4 ESD TRAY**

Outside dim.: 610 x 190 x 252

Portable rack, chrome-plated for
10 trays **A 4-4 N-6-10**
(as depicted)Art. No. **2444186**Designation **A 4-70 ESD TRAY**

Outside dim.: 610 x 190 x 252

Portable rack, chrome-plated for
8 trays **A 4-70 N-6-10**
(as depicted)