

Manual Barrel Loaders

The 560548U Series of manual barrel loaders will fill a barrel directly from a 6 oz, 12 oz, 20 oz, or 300 ml cartridge.

Barrel loaders are connected to an air regulator and set to a pressure suitable for the material not exceeding 65 psi (4.48 bar). A manual switch on the base actuates the air supply and pressurizes the cartridge to fill the syringe barrel.

The barrel fillers' internal air relief valve allows for decompression when the trigger is released. The system can be used for timed filling when connected to a Fisnar automatic controller.



Item Number	Description
-------------	-------------

560548U-6N	6 oz Nylon Barrel Loader
------------	--------------------------

560548U-12N	12 oz Nylon Barrel Loader
-------------	---------------------------

560548U-300	300 ml Metal Barrel Loader
-------------	----------------------------

560548U-570	20 oz Metal Barrel Loader
-------------	---------------------------

Replacement Parts

Item Number	Description
-------------	-------------

561105	1/4" NPT Elbow
--------	----------------

5801451	Syringe Filling Adapter
---------	-------------------------

560710	Luer Lock Cap
--------	---------------

560546	1/4" NPT Polyethylene Female Cartridge Adapter
--------	--

561129	1/4" NPT x 5/8-11 UNC White Acetal Cartridge Adapter
--------	--

562317	1/4" NPT x 13/16-14 UNC Black Acetal Cartridge Adapter
--------	--

Syringe barrel and piston sold separately.