




NOTE:
MATERIAL: zinc alloy
SCREW: STEEL
FINISHED: Nickel plated
ROHS
SERIES NO.
D-SUB METAL HOOD
CONTACT NUMBER:
15PIN
TYPE OPTION:
DB TYPE 90° LONG SCREWS
CABLE ENTRY SIZE:
DIMENSION OF 11.0mm
PARTS OPTION:
LONG SCREW

RoHS Compliant		Ninigi	
APPD. 核准 Betty		UNLESS OTHERWISE SPECIFIED TOLERANCE ANG. 0. ±5° .0 ±0.5 .00 ±0.3 ±0.2	PART NAME 品名 HOOD M04-15T-Y 90° METAL COVER LONG SCREWS WITH SLOTTED INDIVIDUAL PACKAGE ROHS
DWG. 製圖 Lena	SCALE 比例 參考	SIZE. 紙張尺寸 A 4	PART NO. 料號 DSC-815K
DATE 制表日 2024/07/29	UNIT 單位 MM	PAGE 張數 1 / 1	REV. 版次 C